




Diagonal

Electrical height adjustable frame for wall units
Wall units become easily reachable from sitting position
Ideal for nursing homes and institutions




- The Diagonal does not only adjust units by 43 cm but also moves diagonal forward by 18 cm.
- A push button allows control of movement to the wanted position and by a single press the frame returns to top position.
- Standard wall units with height 70-80 cm can be used.
- A safety stop plate is recommended to prevent trapping when lowering.
- Light can be fitted in the safety stop plate to improve visibility.
- Build in measurement (depth of frame) is only 11,5 cm.
- Diagonals are available from 40-180 cm in increments 10 cm.
- Diagonal is also ideal for private homes

Diagonal

Diagonal frame for wall units length 40-120cm



Two connected Diagonals for adjustment of wall units length 130-180cm



Standard Control Switch 6x3cm delivered with frame 30-67840



Accessories


Large Press pad 14x7cm 30-67841



Infrared Hand Control 30-67849



Safety Stop Plate 30-416XX



ROPOX Tips

- Allow a space of 3-5 mm on each side of units for free movement.
- To line up adjacent fixed wall units space them off the wall by 11,5cm.
- Smaller doors of 30/40 cm may be easier to open at worktop height.
- The control switch should be located in the fascia of the worktop below or if this is not a solution a hand control can be a possibility.
- Max load of frames 120 kg, evenly distributed.

ROPOX
BETTER WAYS TO BETTER DAYS

ROPOX A/S
Ringstedgade 221
DK-4700 Næstved
Tel. +45 5575 0500
Fax +45 5575 0550
info@ropox.dk
www.ropox.com